

# PULSAFEEDER®

All MC9000 Systems come standard with a flow assembly and sensor tee mounted to a sturdy polypropylene panel. Optional configurations of the panel can be selected to create a complete chemical injection system. These systems are designed to simplify installation and reduce problems caused by a poor installation. Each panel includes 3/4" plumbing with the following features:

- Quick disconnect sensor mounting tees
- Chemical injection points
- Ball valves on the inlet and outlet
- Back flow check valve
- Flow strainer
- Mounting brackets for chemical metering pumps

Select from one of the following configurations and insert the option code into digit #12 when configuring your controller.

## **Conductivity (Prewire)**

Enter Option "A" in position 12 of the PULSAtron 9000 Model String.

Optional panel selections feature 'quick-disconnect' sensor tees for all parameters; three injectors for inhibitor and biocides and mounting hardware for three pumps. Standard features include ball valves on the inlet and outlet, a back flow check valve before the injection point and a strainer before the sensors to prevent large particles from fouling the sensors. Pump and bleed relays are pre-wired into outlet receptacles (pigtales).

## **Conductivity Panel - Conduit**


Enter Option "C" in position 12 of the PULSAtron 9000 Model String. This option also requires option 'A' in position 7 for conduit.

Panel features 'quick-disconnect' sensor tee; three injectors for inhibitor and biocides; and mounting hardware for three pumps. Pump and bleed relays are wired into a watertight outlet box with a splash guard cover.

**\*NOTE:** The sensor tee is capped on systems that do not require it.

## **Operating Benefits**

- Simplify installation.
- Complete chemical injection system.



## **Aftermarket**

- Solenoids
- Motorized Ball Valves
- Water Meters
- Corrosion Coupon Racks
- Metering Pumps (PULSAtron, XP Series)




**PULSAtron®**  
**Prefabricated Systems**  
**Conductivity**


# PULSATrol® Prefabricated Systems

## Specifications and Model Selection

### Option "A" - Conductivity (Prewire)



### Option "C" - Conductivity (Conduit)



The charts below show standard receptacle wiring and labeling for conduit units based on model type:

Standard 9200 Panel System Wiring (Conduit)				
Model #	Position #1	Position #2	Position #3	Position #4
MC9210__	Timer #1	Alarm Relay	Utility	Utility
MC9210_A	Timer #1	Bio "A"	Alarm Relay	Utility
MC9210_B	Timer #1	Bio "A"	Bio "B"	Utility
MC9220__	pH Control	Timer #1	Alarm Relay	Utility
MC9220_A	Bio "A"	Bio "A"	Alarm Relay	Utility
MC9220_B	Timer #1	Bio "A"	Bio "B"	Utility
MC9230__	pH Control	Timer #1	Alarm Relay	Utility
MC9230_A	pH Control	Timer #1	Bio "A"	Utility


The Bleed Relay (on applicable models) and Input Power to the Controller is wired through the outlet box for customer hook up.

Standard 9300 Panel System Wiring (Conduit)				
Model #	Position #1	Position #2	Position #3	Position #4
MC9310__	Timer #1	Timer #2	Timer #3	Alarm Relay
MC9320__	ORP Feed	Timer #1	Timer #2	Timer #3
MC9330_A	pH Control	Timer #1	Timer #2	Timer #3
MC9330_B	Acid	Caustic	Timer #1	Timer #2

The Bleed Relay and Input Power to the Controller is wired through the outlet box for customer hook up.

Standard 9500 Panel System Wiring (Conduit)				
Model #	Position #1	Position #2	Position #3	Position #4
MC9510__	Timer #1	Timer #2	Timer #3	Alarm Relay
MC9520__	ORP Feed	Timer #1	Timer #2	Timer #3
MC9530_B	pH Control	Timer #1	Timer #2	Timer #3
MC9530_A	Acid	Caustic	Timer #1	Timer #2
MC9540_A	pH Control	Timer #1	Timer #2	Timer #3
MC9540_B	Acid	Caustic	Timer #1	Timer #2
MC9550_B	pH Control	ORP	Timer #1	Timer #2
MC9550_A	Acid	Caustic	ORP	Timer #1

The Bleed Relay and Input Power to the Controller is wired through the outlet box for customer hook up.



## Dimensions

Panel Dimensions = 36" x 28" (w/h) (91.4cm x 71.1cm)



27101 Airport Road  
Punta Gorda, FL 33982  
Phone: ++1(941) 575-3800  
Fax: ++1(941) 575-4085

www.pulsatron.com



An ISO 9001 Certified Company

CTS005 J14

